

4FRONT 2 - TB3 SEAT

DEALERS DETAILS

Dealers Name			
Order Date			
Address			
	Postcode		
Phone		Email	
PO No		Order Ref	

DELIVERY DETAILS

Dealers Address			
	Postcode		
Quantum Specialist			
Ⓢ Clients Weight (required for suspension settings)			

BASE MODEL

14 Colour Options
 Height Adj. Removable Arm Supports
 Centre Mount Foot Platform
 TB3 Seating
 14" Flat Free Drive Tyres
 2" x 9" Flat Free Rear Castors



SRS Suspension System
 Smart Traction Control
 Q-Logic 3e Control System
 2 x 70 ah Batteries
 6 Mph (9.65 Km/h) 4-Pole Motors
 Max User Weight: 21 st 6lbs. (136 kg)

Standard = Standard Factory Feature
 FOC = Select Instead of Standard Factory Feature

DRIVE WHEELS

3" x 14" Flat Free Black Tyres. <i>With matching colour wheel accents.</i>	Standard
3" x 14" Pneumatic Black Tyres. <i>With matching colour wheel accents.</i>	FOC

COLOURS

Back in Black	Standard	Pretty in Pink	FOC
Green Machine	FOC	Lemon Crush*	FOC
Midnight Blue	FOC	Night Train*	FOC
Electric Blue	FOC	Evolution Orange*	FOC
Blue Jean	FOC	Military Green*	FOC
Deep Purple	FOC	Grey Street*	FOC
Red Corvette	FOC	Raspberry Beret*	FOC

* Extended lead-time.

Please download our free PQ-365 app to view colours and other product features in more detail.



SEAT PACKAGES - SEAT WIDTH

☐	12"-16"W.
☐	16"-20"W.
☐	20"-22"W.
Set width at:	

SEAT PACKAGES - SEAT DEPTH

☐	12"-16"D.
☐	16"-20"D.
☐	20"-22"D.
Set depth at:	

STEALTH SEAT CUSHIONS

☐	No Seat Cushion Required	FOC
☐	Zen SP: Skin Protection, 4-way Stretch, Coolcore Cover. <i>160 Kg weight limit.</i>	Standard
☐	Simplicity G: General Use, Fluid Resistant Stealth-Tek Cover. <i>158.7 Kg weight limit.</i>	FOC
☐	TRU-Comfort 2 SPP: Skin Protection, Positioning, 4-way Stretch Coolcore Cover. <i>158.7 Kg weight limit.</i>	FOC

Please note that seat cushions may not be available in all width and depth combinations. Refer to our Stealth Cushion Order Forms for size availability.

SEAT POSITIONING

☒	Static Seat.				Standard		
	Static Seat to Floor Height. <i>From seat pan.</i>	☐	15"	☐	16"	☐	17"

BACKREST SPECIFICATIONS

☐	TRU-Balance 3 Back Support System. <i>Select TB3 back options below. Ignore all 'Back Cane' options.</i>	Standard
☐	Back Canes Only System. <i>Not available with Power recline or TB3 flip-back arm supports. Move directly to 'Back Cane Only Support Options' if selected.</i>	FOC

Select one option above. Both options above include a metal active contour back support shell, TRU-Comfort 2 back cushion, and a set of wedge inserts.

TB3 BACK SUPPORT

☒	Active Contour Back Support with TRU-Comfort 2 Back Cushion and Wedge Inserts. <i>Select size in Back Support Dimensions</i>	Standard
-------------------------------------	--	----------

TB3 BACK SUPPORT POSITIONING

☐	TRU-Balance 3 Static Back. <i>Angle can be preset manually.</i>	Standard
☐	TRU-Balance 3 Flip-forward Back. <i>Not available with TB3 flip-back arm supports or 12"-14"W seats.</i>	FOC

BACK CANE ONLY SUPPORT

☐	Active Contour Back Support with TRU-Comfort 2 Back Cushion and Wedge Inserts. <i>Select size in Back Support Dimensions.</i>					FOC
Back Cane Only Support Positioning.	☐	Tool Angle Adjustable. <i>85° to 120° in 5° increments.</i>				Standard
	☐	☐	☐	☐	☐	
Back Cane Height. <i>From seat pan.</i>	☐	16"H.	17"H.	18"H.	19"H.	20"H.
	☐	21"H.	22"H.	23"H.	24"H.	25"H.

BACK SUPPORT DIMENSIONS

Compatible with TB3 and Back Canes options above. Back Support can be +/- 4" of seat width with TB3 Back Support System, but must be same as seat width with Back Canes Only System.

Backrest Support Width Package.		12"-14"W.	14"-16"W.	16"-20"W.
		18"-22"W.	20"-24"W.	
Back Support Width.	12"W.	14"W.	15"W.	16"W.
	17"W.	18"W.	19"W.	20"W.
	21"W.	22"W.	23"W.	24"W.
Back Support Height. <i>From seat pan.</i>	14"H. <i>12"W back only.</i>	15"H. <i>12"W back only.</i>	16"H.	17"H.
	18"H.	19"H.	20"H.	21"H.
	22"H.	23"H.	24"H.	25"H. <i>Not available with 24"W back.</i>
	26"H. <i>Not available with 24"W back.</i>	27"H. <i>Not available with 24"W back.</i>	28"H. <i>Not available with 24"W back.</i>	

19" minimum backrest height when powered recline is selected.

ARM SUPPORTS

2-Post Flip-up Removable. <i>Adjustment range 9" to 13" from seat pan.</i>	Standard
Paediatric Single Post Height Adjustable. <i>Adjustment range 7.75"- 9.75" from seat pan. 10" pads only.</i>	FOC
Single Post Drop-in Removable. <i>Adjustment range 11"-17" from seat pan.</i>	FOC
TB3 Flip-back. <i>Adjustment range 8"-16" from seat pan. Includes lateral in/out adjustment. Not available with back canes.</i>	FOC
Arm Support Pads.	10" Standard Standard 10" Waterfall. FOC
	14" Standard FOC 14" Waterfall. FOC

CENTRE MOUNTED LEG SUPPORTS

Manually Adjustable Centre Mount Foot Platform.	Standard
Paediatric Adj. Centre Mount Foot Platform. <i>12"-14" seat widths only.</i>	FOC
Lower Leg Extensions. <i>From seat pan.</i>	8"-12". <i>Paediatric centre mount only.</i> FOC 10"-16". Standard 13"-19". FOC
Footplates.	10"W x 6"D Split Footplates. <i>Paediatric centre mount only.</i> FOC
	10"W x 8"D Split Footplates. FOC 10"W x 11"D Split Footplates. Standard
Calf Support.	Individual Calf Pads. <i>6"W x 6"H.</i> Standard

Certain configurations may result in reduced ground clearance below footplates. Contact Quantum Technical for information.

INDIVIDUALLY MOUNTED LEG SUPPORTS

70° Swing-away. <i>Flip-up footplates. Adj. range 12" to 15". Minimum seat width 15".</i>	FOC
Manual Elevating Swing-Away. <i>Flip-up footplates. Adj. range 15" to 20". Min. seat width 15".</i>	FOC

INDIVIDUALLY MOUNTED CONFIGURABLE LEG SUPPORTS

60° to 90°	60° to 90° Tool Adjustable Swing-away Leg Supports. <i>Select lowers and footplates below. Minimum seat width 15".</i>	FOC
Lower Leg Extensions. <i>From seat pan.</i>	11"-13" FOC 13.5"-16.5" Standard 15.5"-19.5" FOC	
	Footplate Type. Angle & Depth Adjustable. <i>6"W x 8"D.</i>	Standard

STEALTH HEAD SUPPORTS

☐	UniLink 8" Comfort Plus. <i>HMO475-17M / CP08CCFPM.</i>	FOC
☐	UniLink 10" Comfort Plus. <i>HMO475-17M / CP10CCFPM.</i>	Standard
☐	UniLink 14" Comfort Plus. <i>HMO475-17M / CP14CCFPM.</i>	FOC

PELVIC BELTS

☒	Auto Buckle Lap Belt, Push Button Release.	Standard
-------------------------------------	--	----------

EXPANDABLE CONTROLS

☒	Q-Logic 3e Controls.	Standard
Control Method.	☐ Hand Control. <i>Select position in Hand Control Mounts below.</i>	Standard
	☐ Attendant Control. <i>Hand control mounted at rear.</i>	FOC

HAND CONTROL MOUNTS

☐	Fixed.	Standard
☐	Basic Swing-away.	FOC
Mounting Position.	☐ Left FOC ☐ Right Standard	

SPEED PROGRAM & LIGHTS PACKAGE

☐	6 Mph Program with Lights and indicators.	Standard
☐	4 Mph Program with Lights and indicators.	FOC
☐	LED Fender Lights. <i>Includes single switch button mounted to side rail. Not road legal.</i>	Standard
☐	Omit LED Fender Lights.	FOC

NOTES & SPECIAL REQUESTS



Quantum®
 32 Wedgwood Road, Bicester,
 Oxon, OX26 4UL
 Phone: 01869 324600
 Fax: 01869 323070
 Email: sales@quantumrehab.co.uk
 Web: www.quantumrehab.co.uk
MOTABILITY ID 714946 - 01/04/25 V1

