

EDGE 3 STRETTO TB FLEX SEAT / POWER TILT / POWER RECLINE / POWER FOOT SUPPORTS

DEALERS DETAILS

Dealers Name

Order Date

Address

Postcode

Phone Email

PO No Order Ref

DELIVERY DETAILS

Dealers Address

Postcode

Quantum Specialist

Ⓢ Clients Weight (required for suspension settings)

BASE MODEL

- 14 Colour Options
- Height Adj. Removable Arm Supports
- 12.5" Flat Free Drive Tyres
- 2" x 5" Flat Free Front Castors
- 2" x 6" Flat Free Rear Castors



- SRS Suspension System
- Q-Logic 3e Control System
- 2 x 40 ah Batteries
- 4 Mph (6 Km/h) Motors
- Max User Weight: 21 st 6lbs. (136 kg)

Standard = Standard Factory Feature
FOC = Select Instead of Standard Factory Feature

DRIVE WHEELS

3" x 12.5" Flat Free Black Tyres.	Standard
3" x 12.5" Pneumatic Black Tyres.	FOC
3" x 14" Flat Free Black Tyres. <i>With matching colour wheel accents.</i>	FOC
3" x 14" Pneumatic Black Tyres. <i>With matching colour wheel accents.</i>	FOC

COLOURS

Back in Black	Standard	Pretty in Pink	FOC
Green Machine	FOC	Lemon Crush*	FOC
Midnight Blue	FOC	Night Train*	FOC
Electric Blue	FOC	Evolution Orange*	FOC
Blue Jean	FOC	Military Green*	FOC
Deep Purple	FOC	Grey Street*	FOC
Red Corvette	FOC	Raspberry Beret*	FOC

* Extended lead-time.

Please download our free PQ-365 app to view colours and other product features in more detail.



STANDARD SEAT DIMENSIONS

15" Width	FOC	16" Width	FOC	15" Depth	FOC	16" Depth	FOC
17" Width	FOC	18" Width	Standard	17" Depth	FOC	18" Depth	Standard
19" Width	FOC	20" Width	FOC	19" Depth	FOC	20" Depth	FOC

STEALTH SEAT CUSHIONS

No Seat Cushion Required	FOC
Zen SP: Skin Protection, 4-way Stretch, Coolcore Cover. <i>160 Kg weight limit.</i>	Standard
Simplicity G: General Use, Fluid Resistant Stealth-Tek Cover. <i>158.7 Kg weight limit.</i>	FOC
TRU-Comfort 2 SPP: Skin Protection, Positioning, 4-way Stretch Coolcore Cover. <i>158.7 Kg weight limit.</i>	FOC

Please note that seat cushions may not be available in all width and depth combinations. Refer to our Stealth Cushion Order Forms for size availability.

SEAT POSITIONING

✓ Powered Seat Tilt. <i>0° to 30°. Uses 1 power option.</i>	Standard			
Powered Tilt Seat to Floor Height. <i>From seat pan.</i>	<table border="1"> <tr> <td>17.5"</td> <td>18.5"</td> <td>19.5"</td> </tr> </table>	17.5"	18.5"	19.5"
17.5"	18.5"	19.5"		

STANDARD BACK SUPPORT POSITIONING *Compatible with standard seat dimensions.*

✓ Powered Back Recline. <i>Adj. range 95° to 125°. Uses 1 power option.</i>	Standard
---	----------

STANDARD BACK SUPPORTS

✓ TRU-Comfort 2. <i>4-way stretch cover. Adjustable range 24.5" to 28" from seat board.</i>	Standard
---	----------

ARM SUPPORTS

TB Flex Removable, Quick Release. <i>Adjustment range 9" to 14" from seat pan.</i>	Standard								
2-Post Flip-up Removable. <i>Adjustment range 9" to 13" from seat pan.</i>	FOC								
Single Post Height Adjustable. <i>Adjustment range 11"-17" from seat pan.</i>	FOC								
Paediatric Single Post Height Adjustable. <i>Adjustment range 7.75"-9.75" from seat pan. 10" pads only.</i>	FOC								
Arm Support Pads	<table border="1"> <tr> <td>10" Standard</td> <td>Standard</td> <td>10" Waterfall. <i>Not with Std flip-up or TB Flex.</i></td> <td>FOC</td> </tr> <tr> <td>14" Standard</td> <td>FOC</td> <td>14" Waterfall. <i>Not with Std flip-up or TB Flex.</i></td> <td>FOC</td> </tr> </table>	10" Standard	Standard	10" Waterfall. <i>Not with Std flip-up or TB Flex.</i>	FOC	14" Standard	FOC	14" Waterfall. <i>Not with Std flip-up or TB Flex.</i>	FOC
	10" Standard	Standard	10" Waterfall. <i>Not with Std flip-up or TB Flex.</i>	FOC					
14" Standard	FOC	14" Waterfall. <i>Not with Std flip-up or TB Flex.</i>	FOC						

CENTRE MOUNTED LEG SUPPORTS *Maximum user weight 113.4 kg.*

Power Elevating Articulating Centre Mount Foot Platform. <i>Uses 1 power option.</i>	FOC				
Lower Leg Extensions. <i>From seat pan.</i>	<table border="1"> <tr> <td>10"-16"</td> <td>Standard</td> </tr> </table>	10"-16"	Standard		
10"-16"	Standard				
Foot Supports.	<table border="1"> <tr> <td>10"W x 8"D Split Foot Supports.</td> <td>FOC</td> </tr> <tr> <td>10"W x 11"D Split Foot Supports.</td> <td>Standard</td> </tr> </table>	10"W x 8"D Split Foot Supports.	FOC	10"W x 11"D Split Foot Supports.	Standard
	10"W x 8"D Split Foot Supports.	FOC			
10"W x 11"D Split Foot Supports.	Standard				
Calf Support.	<table border="1"> <tr> <td>Individual Calf Pads. <i>6"W x 6"H.</i></td> <td>Standard</td> </tr> </table>	Individual Calf Pads. <i>6"W x 6"H.</i>	Standard		
Individual Calf Pads. <i>6"W x 6"H.</i>	Standard				

INDIVIDUALLY MOUNTED CONFIGURABLE LEG SUPPORTS

Power Elevating Articulating Swing-Away Leg Supports. <i>Includes calf pads.</i>	FOC																					
ELEVATING ARTICULATING	<table border="1"> <tr> <td>Lower Leg Extensions. <i>From seat pan.</i></td> <td> <table border="1"> <tr> <td>9"-15"</td> <td>FOC</td> <td>13"-21"</td> <td>Standard</td> </tr> </table> </td> </tr> <tr> <td>Footplate Type.</td> <td>Angle Adjustable Flip-up. <i>Select size below.</i></td> <td>Standard</td> </tr> <tr> <td>Foot Support Size. <i>Includes heel loops.</i></td> <td> <table border="1"> <tr> <td>4"W x 6"D. <i>14" seat widths and above.</i></td> <td>FOC</td> <td>5"W x 7"D. <i>16" seat widths and above.</i></td> <td>FOC</td> <td>6"W x 8"D. <i>18" seat widths and above.</i></td> <td>FOC</td> </tr> </table> </td> </tr> <tr> <td>Powered Leg Support Operation Method.</td> <td> <table border="1"> <tr> <td>Independent. <i>Uses 2 power options.</i></td> <td>Combined. <i>Uses 1 power option.</i></td> </tr> </table> </td> </tr> </table>	Lower Leg Extensions. <i>From seat pan.</i>	<table border="1"> <tr> <td>9"-15"</td> <td>FOC</td> <td>13"-21"</td> <td>Standard</td> </tr> </table>	9"-15"	FOC	13"-21"	Standard	Footplate Type.	Angle Adjustable Flip-up. <i>Select size below.</i>	Standard	Foot Support Size. <i>Includes heel loops.</i>	<table border="1"> <tr> <td>4"W x 6"D. <i>14" seat widths and above.</i></td> <td>FOC</td> <td>5"W x 7"D. <i>16" seat widths and above.</i></td> <td>FOC</td> <td>6"W x 8"D. <i>18" seat widths and above.</i></td> <td>FOC</td> </tr> </table>	4"W x 6"D. <i>14" seat widths and above.</i>	FOC	5"W x 7"D. <i>16" seat widths and above.</i>	FOC	6"W x 8"D. <i>18" seat widths and above.</i>	FOC	Powered Leg Support Operation Method.	<table border="1"> <tr> <td>Independent. <i>Uses 2 power options.</i></td> <td>Combined. <i>Uses 1 power option.</i></td> </tr> </table>	Independent. <i>Uses 2 power options.</i>	Combined. <i>Uses 1 power option.</i>
	Lower Leg Extensions. <i>From seat pan.</i>	<table border="1"> <tr> <td>9"-15"</td> <td>FOC</td> <td>13"-21"</td> <td>Standard</td> </tr> </table>	9"-15"	FOC	13"-21"	Standard																
	9"-15"	FOC	13"-21"	Standard																		
	Footplate Type.	Angle Adjustable Flip-up. <i>Select size below.</i>	Standard																			
Foot Support Size. <i>Includes heel loops.</i>	<table border="1"> <tr> <td>4"W x 6"D. <i>14" seat widths and above.</i></td> <td>FOC</td> <td>5"W x 7"D. <i>16" seat widths and above.</i></td> <td>FOC</td> <td>6"W x 8"D. <i>18" seat widths and above.</i></td> <td>FOC</td> </tr> </table>	4"W x 6"D. <i>14" seat widths and above.</i>	FOC	5"W x 7"D. <i>16" seat widths and above.</i>	FOC	6"W x 8"D. <i>18" seat widths and above.</i>	FOC															
4"W x 6"D. <i>14" seat widths and above.</i>	FOC	5"W x 7"D. <i>16" seat widths and above.</i>	FOC	6"W x 8"D. <i>18" seat widths and above.</i>	FOC																	
Powered Leg Support Operation Method.	<table border="1"> <tr> <td>Independent. <i>Uses 2 power options.</i></td> <td>Combined. <i>Uses 1 power option.</i></td> </tr> </table>	Independent. <i>Uses 2 power options.</i>	Combined. <i>Uses 1 power option.</i>																			
Independent. <i>Uses 2 power options.</i>	Combined. <i>Uses 1 power option.</i>																					

STEALTH HEAD SUPPORTS

<input type="checkbox"/>	UniLink 8" Comfort Plus. <i>HMO475-17M / CP08CCFPM.</i>	FOC
<input type="checkbox"/>	UniLink 10" Comfort Plus. <i>HMO475-17M / CP10CCFPM.</i>	Standard
<input type="checkbox"/>	UniLink 14" Comfort Plus. <i>HMO475-17M / CP14CCFPM.</i>	FOC

PELVIC SOLUTIONS

<input checked="" type="checkbox"/>	Auto Buckle Lap Belt, Push Button Release.	Standard
-------------------------------------	--	----------

NON-EXPANDABLE CONTROLS

<input checked="" type="checkbox"/>	Q-Logic 3e Controls. <i>5 power option ready.</i>	Standard
Control Method.	<input type="checkbox"/> Hand Control. <i>Select position in Hand Control Mounts below.</i>	Standard
	<input type="checkbox"/> Attendant Control. <i>Hand control mounted at rear.</i>	FOC

HAND CONTROL MOUNTS

<input type="checkbox"/>	Fixed.	Standard
<input type="checkbox"/>	Basic swing-away.	FOC
Mounting Position.	<input type="checkbox"/> Left	FOC
	<input type="checkbox"/> Right	Standard

SPEED PROGRAM & LIGHTS PACKAGE

<input checked="" type="checkbox"/>	4 Mph Program. <i>Lights and indicators not included.</i>	Standard
-------------------------------------	---	----------

NOTES & SPECIAL REQUESTS



Quantum®
 32 Wedgwood Road, Bicester,
 Oxon, OX26 4UL
 Phone: 01869 324600
 Fax: 01869 323070
 Email: sales@quantumrehab.co.uk
 Web: www.quantumrehab.co.uk
Motability ID 1003174 - 01/07/25 V1

