

Q6 EDGE 2.0 WITH TB3 SEAT / POWER TILT / ADI BACK SUPPORT

DEALERS DETAILS

Dealers Name	
Order Date	
Address	
Postcode	
Phone	Email
PO No	Order Ref

DELIVERY DETAILS

Dealers Address	
Postcode	
Quantum Specialist	
Ⓞ Clients Weight	

BASE MODEL

- 12 Colour Options
- Height Adj. Removable Arm Supports
- Centre Mount Foot Platform
- TB3 Seating
- 14" Flat Free Drive Tyres
- 2" x 6" Flat Free Front Castors



- 2" x 6" Flat Free Rear Castors
- ATX Suspension System
- QLNES Control System
- 2 x 62 ah Batteries
- 4 Mph (6 Km/h) 4-Pole Motors
- Max User Weight: 21 st 6lbs. (136 kg)

Standard = Standard Factory Feature
FOC = Select Instead of Standard Factory Feature

DRIVE WHEELS

3" x 14" Flat Free Black Tyres. <i>With matching colour wheel accents.</i>	Standard
3" x 14" Pneumatic Black Tyres. <i>With matching colour wheel accents.</i>	FOC

COLOURS

Back in Black	Standard	Red Corvette	FOC
Green Machine	FOC	Lemon Crush*	FOC
Midnight Blue	FOC	Night Train*	FOC
Electric Blue	FOC	Evolution Orange*	FOC
Pretty in Pink	FOC	Military Green*	FOC
Deep Purple	FOC	Grey Street*	FOC

* Extended lead-time.

Please download our free PQ-365 app to view colours and other product features in more detail.



SEAT PACKAGES - SEAT WIDTH

<input type="checkbox"/>	12"-16"W.
<input type="checkbox"/>	14"-16"W.
<input type="checkbox"/>	16"-20"W
<input type="checkbox"/>	20"-22"W
Set width at: <input type="text"/>	

SEAT PACKAGES - SEAT DEPTH

<input type="checkbox"/>	12"-16"D.
<input type="checkbox"/>	14"-16"D.
<input type="checkbox"/>	16"-20"D
<input type="checkbox"/>	20"-22"D
Set depth at: <input type="text"/>	

STEALTH SEAT CUSHIONS

<input type="checkbox"/>	No Seat Cushion Required	FOC
<input type="checkbox"/>	Simplicity G: General Use, Fluid Resistant Stealth-Tek Cover. <i>158.7 Kg weight limit.</i>	Standard
<input type="checkbox"/>	Zen SP: Skin Protection, 4-way Stretch, Coolcore Cover. <i>160 Kg weight limit.</i>	FOC
<input type="checkbox"/>	TRU-Comfort 2 SPP: Skin Protection, Positioning, 4-way Stretch Coolcore Cover. <i>158.7 Kg weight limit.</i>	FOC

Please note that seat cushions may not be available in all width and depth combinations. Refer to our Stealth Cushion Order Forms for size availability.

SEAT POSITIONING

<input type="checkbox"/>	TRU-Balance 3 Powered Seat Tilt. <i>0° to 50° COG tilt. Uses 1 power option.</i>	Standard
Powered Tilt Seat to Floor Height. <i>From seat pan.</i>		<input type="checkbox"/> 17.5" <input type="checkbox"/> 18.5" <input type="checkbox"/> 19.5"

BACKREST SPECIFICATIONS

<input type="checkbox"/>	TRU-Balance 3 Back Support System. <i>Select ADI Q-Back 2 options below. Ignore all 'Back Cane' options.</i>	Standard
<input type="checkbox"/>	Back Canes Only System. <i>Not available with TB3 flip-back arm supports. Move directly to 'Back Cane Only Support Options' if selected.</i>	FOC

Select one option above. Both options above include a metal active contour back support shell, TRU-Comfort 2 back cushion, and a set of wedge inserts.

TB3 BACK SUPPORT

<input type="checkbox"/>	ADI Q-Back 2. <i>Skin protection, 4 way stretch, Coolcore cover. Mounts directly to TB3 system.</i>	Standard
Enter ADI Q-Back 2 part number here. <input type="text"/>		

TB3 BACK SUPPORT POSTIONING

<input type="checkbox"/>	TRU-Balance 3 Static Back. <i>Angle can be preset manually.</i>	Standard
--------------------------	---	----------

BACK CANE ONLY SUPPORT

<input type="checkbox"/>	ADI Back Support. <i>Skin protection, 4 way stretch, Coolcore cover. Mounts to canes with cane clamps.</i>	Standard
Enter ADI Back Support part number here. <input type="text"/>		
<input type="checkbox"/>	Back Cane Only Support Positioning. <input type="checkbox"/> Tool Angle Adjustable. <i>85° to 120° in 5° increments.</i>	Standard
Back Cane Height.	<input type="checkbox"/> 16"H. <input type="checkbox"/> 17"H. <input type="checkbox"/> 18"H. <input type="checkbox"/> 19"H. <input type="checkbox"/> 20"H.	
<i>From seat pan.</i>	<input type="checkbox"/> 21"H. <input type="checkbox"/> 22"H. <input type="checkbox"/> 23"H. <input type="checkbox"/> 24"H. <input type="checkbox"/> 25"H.	

ARM SUPPORTS

2-Post Flip-up Removable. <i>Adjustment range 9" to 13" from seat pan. Minimum seat depth 16".</i>					Standard
Paediatric Single Post Drop-in Removable. <i>Adjustment range 7.75"- 9.75" from seat pan. 10" pads only.</i>					FOC
Single Post Drop-in Removable. <i>Adjustment range 11"-17" from seat pan. Minimum seat depth 14".</i>					FOC
TB3 Flip-back. <i>Adjustment range 8"-16" from seat pan. Includes lateral in/out adjustment.</i>					FOC
Arm Support Pads.	10" Standard	Standard	10" Waterfall. <i>Not with TB3 Flip-back</i>		FOC
	14" Standard	FOC	14" Waterfall. <i>Not with TB3 Flip-back</i>		FOC

CENTRE MOUNTED LEG SUPPORTS

Manually Adjustable Centre Mount Foot Platform. <i>Minimum seat width 14".</i>					Standard	
Paediatric Adj. Centre Mount Foot Platform. <i>12"-14" seat widths only.</i>					FOC	
Lower Leg Extensions. <i>From seat pan.</i>	8"-12". <i>Paediatric centre mount only.</i>	FOC	10"-16".	Standard	13"-19".	FOC
Foot Supports.	10"W x 6"D Split Foot Supports. <i>Paediatric centre mount only.</i>					FOC
	10"W x 8"D Split Foot Supports.	FOC	10"W x 11"D Split Foot Supports.	Standard		
Calf Support.	Individual Calf Pads. <i>6"W x 6"H.</i>					Standard

INDIVIDUALLY MOUNTED LEG SUPPORTS

70° Swing-Away. <i>Flip-up footplates. Adj. range 12" to 15". Minimum seat width 15".</i>					FOC
Manual Elevating Swing-Away. <i>Flip-up footplates. Adj. range 15" to 20". Min. seat width 15".</i>					FOC

INDIVIDUALLY MOUNTED CONFIGURABLE LEG SUPPORTS

60° to 90° Tool Adjustable Swing-Away. <i>Angle & depth adjustable footplates 6"W x 8"D. Select lowers below. Minimum seat width 15"</i>					FOC	
Lower Leg Extensions. <i>From seat pan.</i>	11"-13"	FOC	13.5"-16.5"	Standard	15.5"-19.5"	FOC

STEALTH HEAD SUPPORTS

UniLink 8" Comfort Plus. <i>HMO475-17M / CP08CCFPM.</i>					FOC
UniLink 10" Comfort Plus. <i>HMO475-17M / CP10CCFPM.</i>					Standard
UniLink 14" Comfort Plus. <i>HMO475-17M / CP14CCFPM.</i>					FOC

NON-EXPANDABLE CONTROLS

✓ QLNES Controls. <i>2 power option ready.</i>					Standard
Control Method.	Hand Control. <i>Select position in Hand Control Mounts below.</i>				Standard
	Attendant Control. <i>Hand control mounted at rear.</i>				FOC

HAND CONTROL MOUNTS

Fixed.	Standard
Basic swing-away.	FOC
Mounting Position. <input type="checkbox"/> Left <input type="checkbox"/> Right	

SPEED PROGRAM & LIGHTS PACKAGE

2-Pole Motors & 4 Mph Program with Lights and indicators.	Standard
2-Pole Motors & 6 Mph Program with Lights and indicators.	FOC

ACCESSORIES

Prepare Chassis for Dahl Docking System. <i>Dahl system not included.</i>	FOC
---	-----

NOTES & SPECIAL REQUESTS

Large yellow rectangular area for notes and special requests.



Quantum®
32 Wedgwood Road, Bicester,
Oxon, OX26 4UL
Phone: 01869 324600
Fax: 01869 323070
Email: sales@quantumrehab.co.uk
Web: www.quantumrehab.co.uk
MOTABILITY ID 714914 - 01/07/25 V1

